



[Zoom](#) | [2](#) | [3](#) | [4](#) |

Machine can pack:

- books and blocks of books
- cosmetics and perfumes
- candy and confectionery
- BD, DVD, CD discs
- coffee and tea
- cigarettes
- gift sets
- soap
- etc

Machine is used for packing of more bulky items than in LM-180 and TS-200, such as boxes of candies, tea, cigarettes, perfumes etc.

There is a separate temperature control on both thermo electric heaters, automatic maintenance of temperature in prescribed limits, separate indication of machine's thermo electric heaters heating, possibility to turn off 1 thermo electric heater.

TS-380 has two major differences from the LM-180 and TS-200. The first difference is a thermo table of larger size, which makes the TS-380 more attractive for the packaging of non-standard bulky items (sets of multiple CD/DVD/BD discs, boxes of chocolates, cigarettes, perfumes etc), the thermo shrink also can be performed on the thermo table. The second distinguishing feature is the increased width of the machine, that allows you to install packing film having width of up to 380 mm.

The quality of the packing depends on operator's skill. As a rule two hours is enough in order operator could start to work on machine pretty confidently. Machine's capabilities and operator's qualification allows to get a high quality of the packed box even without an additional thermo shrink. The DVD containing video film with instruction on operation is applied to the machine.

The machine is dependable and not difficult in operation.

Having installed on machine a tear tape [dispenser](#) (which is sold separately) you can pack articles with tear [tape](#). The tear tape is unwound simultaneously with polypropylene film and automatically sticks to it. So, the use of this option does not draw operator's attention away from process and does not complicate his operation.

**Engineering data**

Productivity	200 packs per hour
Envelope shaping	manual
Cutting-off of the film	automatic
Temperature range	130...170 °C
Temperature stability	± 4 °C
Electric power supply for the thermo electric heater and cutting wire	18...24 Volts
Film type	biaxial oriented polypropylene
Film thickness	20...40 micrometers
Maximal width of roll	380 mm
Maximal roll diameter	370 mm
Internal roll diameter	76 mm
Mode of operation	twenty-four-hour
Type of packing	<a href="#">envelope</a>
Dimension, L * W * H	640 * 430 * 255 mm
Dimension in package	645 * 430 * 210 mm
Weight netto/brutto	20,5 / 21,5 kg
Power consumption	200 Watts
Maximal consumption current	2.36 A